

Insert label - EMT (62X10)R - 0800057

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Snap-in marker, for marking Inline modules

The figure shows the EMT (50/28x13)R version

Why buy this product

- Can be printed using all the thermal transfer printers available from Phoenix Contact
- Insertable conductor marking for marking collars
- Thanks to their special shape, insert labels remain securely inside the collar once inserted
- Insert labels for marking various marking collars
- Precise printing quality
- EMT ... insert strips are available in various sizes for marking Inline modules

Key Commercial Data

| | |
|--------------------------------------|-----------|
| Packing unit | 1 STK |
| Weight per Piece (excluding packing) | 240.000 g |
| Custom tariff number | 39269092 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|------------|-------|
| Length (b) | 62 mm |
| Width (a) | 10 mm |

Ambient conditions

| | |
|---------------------------------|--------------------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
| Recommended storage conditions | 23 °C / 50 % relative humidity |

General

| | |
|------------|--------------------------------|
| Color | white |
| Components | free from silicone and halogen |
| Material | Polyester |

Insert label - EMT (62X10)R - 0800057

Technical data

General

| | |
|---|-------------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 500 |
| Number of individual labels per row | 1 |
| RoHS compliant | Yes |
| Printability | Thermal transfer |
| Device | 5146477 THERMOMARK ROLL |
| | 5145274 THERMOMARK X1.1 |
| | 5146231 THERMOMARK X1.2 |
| | 5145313 THERMOMARK S1 |
| | 5146257 THERMOMARK S1.1 |
| Ink ribbon | 5145384 THERMOMARK-RIBBON 110 |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Wipe resistance test result | Test passed |
| Salt spray test specification | DIN EN ISO 9227:2012-09 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Alternating condensation climate with SO2 test specification | DIN 50018:2013-05 |
| Climate level | AHT 1.0 S |
| Cycles | 2 |
| Condensation test result | Test passed |
| Foil strength | 175 µm |
| Marking mounting type | snapped into marker carrier |

Standards and Regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

Insert label - EMT (62X10)R - 0800057

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 8.0 | 27149129 |
| eCl@ss 9.0 | 27400629 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC001694 |
| ETIM 5.0 | EC001288 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300 m, Width: 110 mm, Color: black